# **LUX-B-ID**

## **Compact Tension/Compression Load Cell**



### Suitable for measuring and controlling loads applied to small-scale presses and press-fitting devices

- High sensitivity
- Waterproof connector

LUX-B-ID

Recommended

ombination

- Stainless steel
- Easy installation

Compact & lightweight design with a screw-shape load receiving portion facilitates easy installation to equipment. Furthermore, the cable is connected using a connector, therefore there are no wring problems, and cable replacement is easy. Work is also possible if the cable is replaced with one resistant to repeated bending (Flexible cable). Please attach a suffix of M1Z3K to the model name.

#### **Specifications**

#### Performance

Rated Capacity	See table below.
Nonlinearity	Within ±0.1% RO
	(2KN or less: Within ±0.15% RO)
Hysteresis	Within ±0.1% RO
	(2KN or less: Within ±0.15% RO)
Repeatability	0.05% RO or less
Rated Output	1.3 mV/V or more
	100 N to 1 kN: 0.9 mV/V or more
	50 N: 0.85 mV/V or more

#### **Environmental Characteristics**

Safe Temperature	-20 to 80°C
Compensated Temperature	-10 to 70°C
Temperature Effect on Zero	Within ±0.005% RO/°C
	(50N to 200N: Within ±0.03% RO/°C)
Temperature Effect on Output	Within ±0.005%/°C

#### **Electrical Characteristics**

Safe Ex	citation	15 V AC or DC			
		(50N to 200N: 10 V AC or DC)			
Recommended Excitation		1 to 10 V AC or DC			
		(50N to 200N: 1 to 5 V AC or DC)			
Input Resistance		375 Ω ±1.5%			
Outpu	t Resistance	350 Ω ±1%			
Cable	Model: TE-45				
	6-conductor (0.08 mm²) chloroprene shielded cable,				
	4.4 mm diameter by	3 m long			
Sensor side: Terminated with a connector plug 213FCW-8P					
	Measuring instrument side: Bared at the tip				
	(Shield wire is not connected to the case.)				

#### **Mechanical Properties**

Safe Overloads	150%
Natural Frequencies	See table below.
Material	SUS (Metallic finish)
Weight	Approx. 260 g (5 to 20KN)
	Approx. 90 g (500N to 2KN)
	Approx. 50 g (200N or less) (Excluding cable)
Degree of Protection	IP67 (IEC 60529)

Models	Rated Capacity	Natural Frequencies (Approx.)	Recommended Tightening Torque		
LUX-B-50N-ID	±50 N	8 kHz			
LUX-B-100N-ID	±100 N	11 kHz	3 N⋅m		
LUX-B-200N-ID	±200 N	14 kHz			
LUX-B-500N-ID	±500 N	16 kHz			
LUX-B-1KN-ID	±1 kN	21 kHz	10 N·m		
LUX-B-2KN-ID	±2 kN	27 kHz			
LUX-B-5KN-ID	±5 kN	18 kHz			
LUX-B-10KN-ID	±10 kN	21 kHz	80 N·m		
LUX-B-20KN-ID	±20 kN	25 kHz			

#### Optional Accessories

Mount base CX (Page 2-48) Ball joint TU (Page 2-75) Whirl-stop coupling TSC (Page 2-48) Whirl-stop brackets TS (Page 2-48)



#### **To Ensure Safe Usage**

If impact is expected in receiving tensile loads, select a load cell with the rated capacity higher by one rank than the operating load.

Physical quantity indication















Outline

Compressive

Tensile

Tensile & compressive

Component

Special

Other

TRANSDUCERS

Outline

Compressive


Tensile


Tensile & compressive


Component

Special

Other









Models	Α	В	С	D
LUX-B-5KN-ID	49	26.5	15	19.5
LUX-B-10KN-ID	51	27.5	16	18
LUX-B-20KN-ID	53	27	16	18

LUX-B-5KN to 20KN-ID

#### ■Dimensions of mount base

#### Mount base CX






Load cells	Mount Bases	φА	φВ	φС	φD	Е	F	G	φН	φЈ	L	$\phi$ M	N	Weight (Approx.)
LUX-B-50N-ID														
LUX-B-100N-ID	CX-2	43	26	9	35	7	2.5	4.5	4.5	5	18±0.1	3 0.20	4.5	40 g
LUX-B-200N-ID														
LUX-B-500N-ID														
LUX-B-1KN-ID	CX-4	48	29	13	39	12	5	7	7	5	21±0.1	4 0.2	6	100 g
LUX-B-2KN-ID														
LUX-B-5KN-ID														
LUX-B-10KN-ID	CX-6	68	44	20	57	20	10	13	13	7	33±0.1	5 0.2 5 0.1	6	350 g
LUX-B-20KN-ID														

Hexagon socket head bolts for connection among load cells, mount bases, and locking pins are attached to the

#### Dimensions in combination with special accessories

#### In combination with mount base (CX)


(The patch should be prepared by user or CA-2F or the equivalent should be used.) (This combination does not apply to tensile load measurement.)



Load Cells	Mount Bases	φА	В
LUX-B-50N-ID			
LUX-B-100N-ID	CX-2	43	33
LUX-B-200N-ID			
LUX-B-500N-ID			
LUX-B-1KN-ID	CX-4	48	49
LUX-B-2KN-ID			
LUX-B-5KN-ID			69
LUX-B-10KN-ID	CX-6	68	71
LUX-B-20KN-ID			73

#### ●In combination with ball joint (TU), whirl-stop coupling (TSC) and whirl-stop bracket (TS)

(This combination does not apply to compressive load measurement.)



<sup>\*</sup>Note that the Whirl-stop Bracket TS is not a safety device to be used when a load exceeding the safe overload is applied. If exceeding safe overload is applied, install a safety device on customer side before use.

Load Cells	Whirl-stop Couplings	Whirl-stop Brackets	Ball Joints	(A)	(B)	С	D	φE	F
LUX-B-50N-ID	TSC-2M								
LUX-B-100N-ID	TSC-2F	TS-2	TU-6B	102	120	44.7	18	6	9
LUX-B-200N-ID	13C-2F								
LUX-B-500N-ID	TSC-4MB								
LUX-B-1KN-ID	TSC-4IVIB	TS-4B	TU-12B	165	195	50.5	30	12	16
LUX-B-2KN-ID	13C-4FB								
LUX-B-5KN-ID	TSC-6MB			237	279				
LUX-B-10KN-ID	TSC-6FB	TS-6R	TU-18B	239	281	67 42	42	18	23
LUX-B-20KN-ID	13C-0FB			241	283				

#### **To Ensure Safe Usage**

•Pay attention to strength of fastened parts which is screwed into the LUX-B. When using the LUX-B with rated capacity more than 2 kN or more, use the fastened parts made of a material with tension strength more than 800 N/mm<sup>2</sup>

Typical recommended material: SUS630 (H900) HRC40 to 47 SCM435 HRC30 to 38 ●For tensile load measurement, take care never to exceed the safe overload rating.



Outline

Compressive

Tensile

Tensile & compressive

Component

Special

Other

Outline


Compressive

Tensile


Tensile & compressive


Component

Other





LUX-B-50N to 200N







Rated Capacity: 500 N








2500 40 60 80 Load in Sensitivity Direction (% RO) Rated Capacity: 2 kN 4000 3000 Bending Mome (N.mm.) 1000 Safe 20 40 60 80 100 Load in Sensitivity Direction (% RO)











# F: 500N (50%RO)

Fig. 1

## Shown here is an example calculating the safe lateral load when the LUX-B-1KN-ID receives a load in sensitivity direction (Vertical direction). (See Fig. 1.)

How to obtain safe lateral loads

The safe lateral load f (N) which is applied to the screw at the distance of 17 mm from the center of the moment when a load of 500 N (50% the rated capacity) is applied in sensitivity direction and is obtained as follows:

According to Graph-1, safe bending moment, M, is approximately 2500 N·m when a load of 50% the rated capacity is applied in sensitivity direction. Since the relation between safe lateral load f, and safe bending moment M is M =  $f \cdot L$ ,

$$f = \frac{M}{L} = \frac{2500}{17} = 147.1N$$

Therefore, the safe lateral load f is 147.1 N.

